

# X-FCP Checker Plate Fastening System

### **Product data**

### **Dimensions**

X-FCP-R 5/10 X-FCP-F 5/10 HILTI (2) \1,25 10 ø 45

### **General Information**

Material specifications

See fastener selection for more details.

### Fastening tool

See fastener selection for more details.

### Approvals

10

ABS: X-FCP-R

LR: X-FCP-R


X-CRM8-15-12 FP10





### X-FCP Sealing ring


ø 45


















## **Application**



Chequer plate

2.155 8/2011



## Load data

## **Recommended loads:**

# $N_{rec} = 1.8 [kN]$


### Conditions:

- Limited by the strength of the X-CRM8 threaded stud
- Recommended loads are valid for fastenings of steel and aluminium with 20 mm pre-drilling.
- X-FCP-F and X-FCP-R are not intended for shear loading.

# **Application requirements**

### Thickness of base material

X-CRM8



Minimum steel thickness t<sub>II</sub> ≥ 6 mm

## Spacing and edge distances

## X-CRM8

Edge distances:  $c \ge 15 \text{ mm}$ Spacing:  $s \ge 15 \text{ mm}$ 





### Thickness of fastened material


Thickness of chequer plates: t₁ ≈ 5.0–13.0 mm

2.156



# **Application limits**


# DX 76, DX 76 PTR



- ① X-CRM8-\_\_-12 FP10 / DX 76 (impact)
- ② X-CRM8-\_\_-12 FP10 / DX 76 (co-acting)

 $t_{II} \ge 6 \text{ mm}$ 

# DX 460



- ① **X-CRM8-\_\_-12 P8** / DX 460 (impact)
- ② X-CRM8-\_\_-12 P8 / DX 460 (co-acting)

 $t_{II} \ge 6 \text{ mm}$ 

#### Note:

For co-acting operation push the fastener all the way back against the piston with a ramrod.

8/2011 2.157



# Fastener selection and system recommendation

# **Application areas**

Marine, offshore, petrochemical, caloric (coal, oil) power plants, etc. lifetime use

### X-FCP system

<b>X-FCP-R</b> Item no. 308860	<b>X-FCP-F</b> Item no. 308859	Sealing ring	Tools
Note:	Note:		SF 100-A, SF 120-A
Not for use in automobile		Drip-through of water/	
tunnels, swimming pools or		oil needs to be prevented	
similar environments	polluted environment.		

#### Threaded studs

Designation	Chequer plate thickness		Tools
X-CRM8-15-12	9–13 mm	DX 460, DX 76, DX 76 PTR	
X-CRM8-9-12	5– 8 mm		DX 460, DX 76, DX 76 PTR
	50 =	2 9	

# Cartridge selection and tool energy setting

Designation	Tools
6.8/11M red cartridges	DX 460
6.8/18M yellow cartridges	DX 76, DX 76 PTR

Tool energy adjustment by setting tests on site.

# Material and coatings

#### X-FCP system

	X-FCP-R		X-FCP-F		All Systems
	1	2	10	<b> </b> 2	3
	Disk	Screw	Disk	Screw	Sealing ring
Material designation	X5CrNiMo17122	X2CrNiMo17132	ST2K40 BK	9SMnPb28 K	Neoprene, black
Coating	none	none	Duplex *	Duplex *	

 $<sup>^{*})</sup>$  480 h Salt spray test per DIN 50021 and 10 cycles Kesternich test per DIN 50018/2.0 (comparable to 45  $\mu m$  HDG steel)

### Threaded studs CRM8

	X-CR shank	CRM8 threaded sleeve	
Material designation	Stainless steel	X2CrNiMo17132	
	wire, CR 500	X5CrNiMo17122+2H	
	(A4 / AISI316)	(A4 / AISI316)	
Coating	none	none	


2.158



# Fastening quality assurance


# **Fastening inspection**

X-CRM8-9-12



 $h_{NVS} = 13 \pm 2 \text{ mm}$ 

#### X-CRM8-15-12




 $h_{NVS} = 18 \pm 2 \text{ mm}$ 


### Installation

## Installation procedure for chequer plates


Plates must be pre-drilled or prepunched



Place and align the plate section




2. Drive the X-CRM threaded stud through



3. Screw the X-FCP on the stud by hand



Tighten the disk



Tightening torque  $T_{rec} = 5-8 \text{ Nm}$ 

# Tightening tool:

- Screwdriver with torque release coupling (TRC)
- S-NSX 2.8 x 15 bit

Hilti Torque Screwdriver setting SF 120-A TRC 5.5-7 SF 150-A TRC 8-9

2.159 8/2011



2.160 8/2011